

Vaisala Differential Pressure Transmitter PDT102



Vaisala Differential Pressure Transmitter PDT102 with process valve actuator and test jacks.

Features

- In-place system calibration and on-line monitoring without disturbing process tubes with optional process valve actuator and test jacks
- Ultrathin profile ideally suited for DIN rail mount reduces installation and calibration costs
- High accuracy, two options; 0.25% or 0.50% of span designed for use in critical monitoring of cleanrooms for pharmaceutical, biotechnology, medical device and semiconductor controlled manufacturing environments
- Extremely robust MEMS silicon sensor technology provides very high accuracy, sensitivity, stability and durability
- NIST traceable 9 point calibration with certificate
- Front side accessible zero and span adjustment potentiometers

Operating Environment

Vaisala Differential Pressure Transmitter PDT102 is a high performance instrument designed primarily for life science and high technology cleanroom applications. The front panel includes zero and span adjustment potentiometers for convenient adjustment. The PDT102 transmitter is ideal for incorporating into the Vaisala Veriteq Continuous Monitoring System to measure and monitor the critical environmental parameters as required in regulated environments.

Performance

The PDT102 offers very high accuracy, sensitivity and stability with two options for accuracy, 0.25% or 0.50% of span providing a highly

reliable and repeatable measurement. The sensor uses a micro-machined, ultra-thin silicon diaphragm which provides inherent sensor repeatability and stability. The sensor enables precise measurement and control in high performance cleanrooms. The PDT102 transmitter is available with voltage output (3-wire) or current output (2-wire).

Available Options

Online monitoring of the PDT102 is simple using the optional process valve actuator and the front access test jacks. The front access test jacks provide online process reference signal or calibration signal without disconnecting power supply wiring. Measurements can be made using a standard multimeter.

Technical Data

Performance

Measurement ranges (bidirectional)	±50 Pa ±0.25 in H ₂ O
Overpressure	
proof pressure	0.7 bar
burst pressure	1.7 bar
static pressure	1.7 bar
Pressure type	differential, gauge, vacuum and compound
Accuracy	0.25 % span or 0.5 % span, depending on choice
Repeatability	
for 0.25 % span accuracy	0.03 %
for 0.5 % span accuracy	0.05 %
Electrical resolution	1 x 10 ⁻⁴ span
Long-term stability	≤0.5 % span/year
Response time (10 ... 90 %)	250 ms
Warm-up time	15 s
Compensated temperature range	+2 ... +57 °C (+35.6 ... +134.6 °F)
Temperature dependence	±0.36 % / 10 K (reference 20 °C (68 °F))
Mounting position	
error (zero adjustable)	≤0.25 %
Adjustments (front accessible)	
zero	±5 % span
span	±3 % span

Operating Environment

Operating temperature	-29 ... +70 °C (-20.2 ... +158 °F)
Storage temperature	-40 ... +82 °C (-40 ... +179.6 °F)
Electromagnetic compatibility (EN 61326-1), basic immunity test requirements	

Note: If used in an electromagnetic field of 3 V/m, with narrow frequency area of 80 - 120 Mhz, it is possible that the current output of PDT102 can deviate max. 0.3% (with accuracy specified 0.25%).

Inputs and Outputs

Process connection	1/8 NPT female according to ANSI/ASME B1.20.1
Output signal	
2-wire	4 ... 20 mA
3-wire	0 ... 5V
Operating voltage	12 ... 36 VDC
Max. loop resistance for 4 ... 20 mA	≤ (Supply voltage - 12V)/0.022 A
Supply current	
for 0 ... 5V output	max. 10 mA
for 4 ... 20 mA output	max. 20 mA
Electrical connection	Screw terminals, 12 ... 22 AWG (0.33 up to 3.31 mm ²)

Mechanics

Medium (measured gas)	clean and dry air, non-conducting and non-corrosive gases
Material	
process connection	brass
sensor element	silicon, aluminium, glass
case	Polycarbonate, glass filled (UL94-V-1)
Mounting	DIN rail types EN 50022, EN 50035 and EN 50045
Housing classification	IP30
Weight	0.16 kg

Dimensions

Dimensions in mm




Figure 1




Figure 2 with Process Valve Actuator and Test Jacks

Order Information for PDT102

PDT102 - XXXT

Measurement range:	
P (+/-50 Pa) or W (+/-0.25 in H ₂ O)	↑
Accuracy: 2 (0.25 % span) or 5 (0.5 % span)	↑
Output: C (current) or V (voltage)	↑
Option: (blank) or T	↑

VAISALA

www.esis.com.au
Ph 02 9481 7420
Fax 02 9481 7267
esis.enq@esis.com.au

Ref. B211083EN-B ©Vaisala 2011
 This material is subject to copyright protection, with all copyrights retained by Vaisala and its individual partners. All rights reserved. Any logos and/or product names are trademarks of Vaisala or its individual partners. The reproduction, transfer, distribution or storage of information contained in this brochure in any form without the prior written consent of Vaisala is strictly prohibited. All specifications — technical included — are subject to change without notice.

